# Technical Datasheet Vitralit® 1680



### **Product Description**

Panacol Vitralit<sup>®</sup> adhesives are one-component, solvent-free radiation-curing adhesives. The advantages are very short curing times, good adhesion to a variety of substrates, and easy handling. Vitralit<sup>®</sup> products are used in electronics, medical applications, optics and for fixing parts in general.

Vitralit® 1680 is a UV-A curing epoxy resin that has been specifically developed as a glob-top chip cover.

Vitralit® 1680 offers the advantages of the chip cover materials of the 1st generation, but it has a better adhesion and climate resistance.

Vitralit<sup>®</sup> 1680 is distinguished by its special purity and low ion content (Na \*, K +, Cl- <5ppm) that makes it suitable for semiconductor applications

#### Suitability on various substrates

PC * AI o steel o PVC ✓	ceramic	✓	PA	0	glass	0	brass	0
	IP(.	*	ΑI	0	steel	0	PVC	✓

<sup>✓</sup> excellent o suitable \* pretreatment necessary/recommended

#### **Curing Properties**

UV-A	VIS	Thermal curing	Activator curing
✓	-	-	-

<sup>✓</sup>suitable - not suitable

The product cures within seconds with radiation in the UV-A - range (320 nm - 390 nm). For rapid and high quality crosslinking we recommend the UV devices manufactured by Dr. Hoenle AG, which complement our adhesive technology.

Bluepoint LED/LED-spot				
Wavelength [nm] 365 405				
Suitability	++	-		

<sup>+</sup> application-related ++ well-suited +++ ideal - not suitable

To obtain full cure at least one substrate must be transparent to the recommended wavelength. The curing speed will depend on the intensity of light, light source, the exposure time, and the light transmittance of the substrate. Increased mechanical properties are achieved after 24 hours.

UV-curing				
Intensity [mW/cm²]	Layer thickness [mm]	Time [sec]		
60	0,5	30		

# **Technical Datasheet**

# Vitralit® 1680



# **Technical Data**

Resin	ероху
Appearance	grey
Filler	quartz
Filler – weight [%]	52
Particle size D95 [µm]	12

## **Uncured material**

Viscosity [mPas] (Brookfield LVT, 25°C, Sp 4, 30rpm) PE-Norm 001	6 000 - 9 000
Density [g/cm³] PE-Norm 004	1,5
Flash point [°C] PE-Norm 050	> 93

## **Cured material**

Hardness shore D PE-Norm 006	70 - 80
Temperature resistance [°C] PE-Norm 065	-40 - 150
Shrinkage [%] PE-Norm 031	1,2
Water absorption [mass %] PE-Norm 016	<0,2

Glass transition temperature DSC [°C] PE-Norm 009	35 - 45
Coefficient of linear expansion [ppm/K] below Tg PE-Norm 017	45,0

Thermal conductivity [W/m*K] PE-Norm 062	0,8
Dielectric constant [10kHz]	3,4

Young's modulus E [MPa] PE-Norm 056	628
Tensile strength [MPa] PE-Norm 014	17,8
Elongation at break [%] PE-Norm 014	8,1

# Technical Datasheet Vitralit® 1680



## Transport/Storage/Shelf Life

Trading unit	Transport	Storage	Shelf-life*	
Cartridge	0°C - 10°C	-20°C - 0°C	at delivery min. 6 months	
Other packages	0 6 - 10 6	-20 C - 0 C	max. 12 months	

<sup>\*</sup>Store in original, unopened containers!

#### **Instructions for Use**

#### Surface preparation

The surfaces to be bonded should be free of dust, oil, grease or other dirt in order to obtain an optimal and reproducible bond.

For cleaning we recommend the cleaner IP® Panacol. Substrates with low surface energy (e.g. polyethylene, polypropylene) must be pretreated in order to achieve sufficient adhesion.

#### Application

Our products are supplied ready to use. Depending on packaging they can be applied by hand directly from the container or semi or fully automatically. With automated application from the cartridge the adhesive is conveyed by a compressed air-operated displacement plunger via a valve in the needle. When metering low viscosity materials from bottles the adhesive is transported by a diaphragm valve. If help is required, please contact our application engineering department.

Adhesive and substrate may not be cold and must be warmed up to room temperature prior to processing.

After application, bonding of the parts should be done quickly. Vitralit<sup>®</sup> adhesives cure slowly in daylight. Therefore, we recommend to expose the material to as little light as possible and the use of opaque hose lines and dispensing needles.

For safety information refer to our safety data sheet.

#### Note

The product is free of heavy metals, PFOS and Phthalates and is conform to the EU-Directive 2011/65/EU "RoHS II" .

Our data sheets have been compiled to the best of our knowledge. The enclosed information describes characteristic properties, with no declaration of commitment. We recommend trials in order to confirm that our products satisfy the particular application requirements. For any additional technical support, please contact our application engineering department. For warranty claims, please refer to our standard terms and conditions.